

Press release  
No. 074/2022

## Convenience features for connoisseurs: The new entry-line ovens from Miele

- ▶ New design with EasyControl Plus user interface
- ▶ All models are connectivity-enabled and sport more than 15 automatic programmes

**Gütersloh/Berlin, August 31, 2022. – Greater elegance, more convenience and increased performance for your money – Miele is further upgrading its successful entry-line oven model from the H 2000 series. The most noticeable modifications are the expansive use of obsidian black glass and the text display. For the first time, too, 15 automatic programmes will be available for the simple and effortless preparation of popular classic dishes. These models are produced at Miele's Oelde plant and are tested to last 20 years.**

At first glance, it is obvious that these new entry-line ovens stand out from their predecessors: an obsidian glass front lends the product its puristic design. Further accents are provided by a combination of an elegant handle which appears to levitate above the frontage and a sliver of trim on the underside of the door – both made from brushed aluminium in stainless look. With their reduced elegance, the new ovens blend in perfectly in particular in open-plan kitchen designs.

For the first time, EasyControl Plus will be introduced to this model series. Two newly designed extra-slim rotary selectors with an aluminium bezel, a text display and additional sensor controls below the display make navigation and programme selection more intuitive and convenient. The 76 l oven interior features five rack levels and, like all Miele models, sports Miele's patented PerfectClean finish with its exceptional non-stick properties. The oven and baking sheets can simply be washed with water with a dash of washing-up liquid added and a sponge. Alternatively, model versions with pyrolytic self-cleaning are also available. This feature incinerates grease splashes and soiling in the oven interior to ash at very high temperatures. Residue can simply be wiped out with a damp cloth.

### Convenient automatic programmes and smart features

Thanks to the 15 automatic programmes, dishes such a fillet of beef, salmon, potato gratin and apple pie are cooked to a T. This dispenses with the need to manually enter operating mode, temperature and cooking time. It also goes without saying that these ovens feature all

the usual heating modes such as 'Hot air Plus', 'Top and Bottom Heat' and a grill. These are now joined by programmes to master specific challenges such as 'Intensive bake' for crusty cake bases and juicy toppings on pizzas, quiches and fruit flans.

All models are connectivity-enabled and can be connected to the Miele App\* via WiFi. This allows users to remotely check on the operating mode, the temperature and the time remaining at any time. If needs be, the temperature and cooking time can be adjusted. And the RemoteUpdate\* function allows available software updates to be downloaded online and installed, ensuring that ovens reflect the state of the art at all times.

The new entry-line ovens have an A+ rating for energy efficiency. The market launch is scheduled for February 2023.

\*The applications for domestic appliances mentioned in the text are additional digital services from Miele & Cie. KG. All smart applications are enabled by the Miele@home system. The range of functions may vary depending on the model and the country.

## Media contact

Julia Cink

Phone: +49 5241 89-1962

Email: [julia.cink@miele.com](mailto:julia.cink@miele.com)

**Company profile:** Miele is the world's leading manufacturer of premium domestic appliances including cooking, baking and steam-cooking appliances, refrigeration products, coffee makers, dishwashers and laundry and floor care products. Their product portfolio also includes dishwashers, air purifiers, washing machines and tumble dryers for commercial use as well as washer-disinfectors and sterilisers for use in medical and laboratory applications. Founded in 1899, the company has eight production plants in Germany, one each in Austria, the Czech Republic, China, Romania and Poland as well as two production plants belonging to its Italian medical technology subsidiary Steelco. Sales in the 2021 business year amounted to around €4.84 bn. Miele is represented with its own sales subsidiaries and via importers in almost 100 countries/regions. Throughout the world, the family-run enterprise, now in its fourth generation, employs a workforce of around 22,300, of which approx. 11,200 employees work in Germany. The company has its headquarters in Gütersloh in Westphalia.

## There are three photographs with this text



**Photo 1:** With their reduced elegance and expansive obsidian black glass, the new ovens blend in perfectly, in particular in open-plan kitchen designs. (Photo: Miele)



**Photo 2:** Ample space: the 76 l oven interior features five rack levels and, like all Miele models, sports Miele's patented PerfectClean finish with its exceptional non-stick properties. (Photo: Miele)



**Photo 3:** All new entry-line ovens are connectivity-enabled and can be connected to the Miele App\* via WiFi. This allows users to remotely check on the operating mode, the temperature and the time remaining at any time. If needs be, the temperature and cooking time can be adjusted. (Photo: Miele)

Text and photo download: [www.miele-press.com](http://www.miele-press.com)

Follow us on:

 @Miele\_Press

 @Miele

 @Miele\_com

 Miele