

Press release
No. 098a/2024

The new generation W2 / T2 "Nova Edition" washing machines and tumble dryers at a glance

W2 Nova Edition

Positioning	Top model of the new W2 generation
New features	<p>InfinityCare honeycomb drum – first ribless drum for even gentler washing</p> <p>SmartMatic – The new automatic programme for all cotton and easy-care textiles that can be washed at 30°C. It guarantees a constant consumption of water and energy per kilo of laundry (up to 4 kg), regardless of the load.</p> <p>FlexLoad – Improved load detection for lower water and electricity consumption in all programmes and up to 2 hours shorter running times</p> <p>MotionReact – The appliance switches on automatically when approached</p> <p>ComfortOpen – Door opens with a gentle touch</p>
Design	<p>New design concept with dark-coloured real glass in the "BlackEffect" colour (control panel and door)</p> <p>25 percent larger motorised door opener</p> <p>New AmbientLight lighting concept makes handling easier</p>
Operation	Larger M Touch Pro display with intuitive touch and Wipe functions and in colour throughout

Free to
editorial
Usage

Please send supporting documents
Miele & Cie. KGP.O. Box
Press and33325 Gütersloh
Public Relations

toPostal addressPhone
05241 89-1953
Fax
05241 89-1950

www.miele.de
89-1953presse@miele.de

Max. Load	9 kg
Spin speed	Depending on model 1,600 rpm or 1,400 rpm
Other functions	TwinDos – Automatic detergent dispensing PowerWash – Innovative washing process for less water and electricity consumption QuickPowerWash – Wash 4kg in just 49 minutes SingleWash – Efficient and fast washing of small quantities SteamCare – Freshen up or smooth clothes with steam – without washing
Further equipment	All-water connection (also hot or rain water)
Networking	Via the Miele app
Recommended retail price	Depending on model € 2,299 or € 2,699
Energy efficiency class	Depending on model A and A - 20 %
Availability	First quarter 2025

T2 Nova Edition

Positioning	Top model of the new generation T2 (TQ 1000 WP)
New features	<p>QuickPowerDry – Tumble drying of 4 kg in just 49 minutes</p> <p>SingleDry – Efficient and fast tumble drying of small load sizes</p> <p>Extra Quick – Reduce programme running time by up to 30 minutes</p> <p>WoolDry – Particularly gentle drying of delicate woollen textiles</p> <p>MotionReact – The appliance switches on automatically when approached</p> <p>ComfortOpen – Door opens with a gentle touch</p>
Design	<p>New design concept with dark-coloured real glass in the "BlackEffect" colour (control panel and door)</p> <p>25 percent larger motorised door opener</p> <p>new AmbientLight lighting concept makes handling easier</p>
Operation	Larger M Touch Pro display with intuitive touch and Wipe functions and in colour throughout
Max. Load	9 kg
Further highlight features	<p>FragranceDos – Gentle scenting of the laundry via Fragrance flacons in different varieties</p> <p>DryCare 40 programme option – Drying of garments that are washable at 40°C, even if the textile is not suitable for the tumble dryer according to the care label*</p>
Networking	Via the Miele app

Recommended retail price	2.499 €
Condensation efficiency class	A
Energy efficiency class	A +++ - 10%
Availability	First quarter 2025

*does not apply to silk and wool