

## The most important milestones in Miele laundry care

- 1901 – 'Meteor' first Miele wooden tub washing machine
- 1930 – Domestic washing machine with metal tub (all-metal washing machine no. 100)
- 1931 – The successful commercial washing machine 00 goes into production
- 1953 – Drum washing machine no. 307 is one of the first washing machines with a porthole door. The machine is loaded from the front for the first time
- 1956 – The first washing machine for commercial applications (W 702)
- 1958 – WVA 505 washing machine for domestic use
- 1962 – Miele single-button automatic Miele 420
- 1966 – First electric tumble dryer for domestic use (T 450)
- 1967 – Europe's first electronically controlled tumble dryer (T 460)
- 1978 – World's first microcomputer control for washing machines
- 1985 – The ten millionth washing machine rolls off the production line
- 1991 – The world's first domestic appliances (washing machines, tumble dryers, dishwashers, microwave oven) with Novotronic - the Miele full electronics - in SMD technology
- 1991 – World record: 1.600 spin cycles
- 1997 – Miele world innovation: Programme for hand-washable wool
- 2000 – First places in international product tests confirm Miele quality
- 2001 – Honeycomb drum; 1.800 spin cycles and Softronic controls
- 2003 – Steel Innovation Award for the honeycomb drum

2007 – The twenty millionth washing machine rolls off the production line

2010 – "AutoDos": The first automatic dispensing system for liquid and powder detergents

2013 – New W1 washing machine series: the washing machines are characterized by a clear and simple user interface and useful additional functions

“TwinDos”: Integrated two-phase dispensing system of liquid detergent

“PowerWash”: energy-efficient and hygienic washing process

“CapDosing”: practical, precise dosing of special detergents, additives and fabric conditioners using capsules.

2014 – Smart grid-capable washing machines: powered by private photovoltaic systems

“InfoControl Plus”: Control of the washing machine via smartphone

2015 – Miele Marine: Washing machines adapted to the requirements of the high seas at sea

2018 – SingleWash: Individual items of clothing can now be washed efficiently and environmentally friendly in just 39 minutes (washing effect A) - with 60% less energy consumption

2022 – For the sake of the climate, Miele completely removes tumble dryers without heat pumps from the programme

2022 – With the WCI 870 Waterproof system and the WWE 360 Waterproof system GreenPerformance, Miele achieves test winner status at Stiftung Warentest for the fifth time in a row

2023 – With the new product category - the Miele Aerium laundry cabinet - textiles can be easily refreshed, smoothed and tumble dried

2024 – At IFA, Miele presents the top models of the new W2 / T2 Nova Edition,

which take an innovative leap forward in terms of laundry care and convenience

- At the heart of the washing machine is the InfinityCare honeycomb drum - the world's first drum without ribs and thus a further development of the legendary Miele honeycomb drum
- SmartMatic automatic programme: For all cotton and Minimum iron fabrics, from 30 degrees, ensures consistent consumption of water, energy and - when using the TwinDos automatic dispensing system - detergent per kg of laundry
- High-quality design combined with intuitive operation: panel and door are made of dark real glass in the color "BlackEffect"; M Touch Pro controls are even larger and in color; AmbientLight
- T2 Nova Edition tumble dryer equipped with convenient QuickPowerDry and WoolDry programmes